





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	NEW RELEASE		19/Jun/2008	
A1	UPDATED CABLE MARKING		23/Apr/2019	



CABLE MARKING:

Amphenol Cables on Demand TYPE CM 24AWG 4PR 75°C (UL)
c(UL) E314104 CMG TIA/EIA-568-B.2 STP CAT.5E LOT NO.



PIN OUT: T568B

PLUG 1	PLUG 2	COLOR
PIN 1	PIN 1	WHITE/ORANGE
PIN 2	PIN 2	ORANGE
PIN 3	PIN 3	WHITE/GREEN
PIN 4	PIN 4	BLUE
PIN 5	PIN 5	WHITE/BLUE
PIN 6	PIN 6	GREEN
PIN 7	PIN 7	WHITE/BROWN
PIN 8	PIN 8	BROWN



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

DECIMALS	ANGLES
X	±X°
XX	±.XX
XXX	±.XXX

THIRD ANGLE PROJECTION



E&R NO.		DATE	
APPROVALS	DATE		
DRAWN	LF	19/Jun/2008	
CHECKED	BA	19/Jun/2008	
RESP ENG			
MFG ENG			

Amphenol Cables on Demand
20 VALLEY ST. ENDICOTT, NY 13760
ASM CBL RJ45/RJ45 CAT.5E
4PR PATCH CORDS

SIZE DWG. NO.
A MP-54RJ45SNNB-007

SCALE SHEET OF
A1

NOTES: UNLESS OTHERWISE SPECIFIED