






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
H	C221973	2022/12/26	Ruru	 XI
I	C231034	2023/08/09	Ruru	 XI
J	C251374	2025/10/27	Vicky	 XI



Recommended
Panel Cut-Out



Pin Assignment Front View

  Note:

- * RoHS Compliant
- *  Important dimension
- *   Waterproof rate: IP68, unmated 1m/24h
 IP69K, mated
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - O-Ring: Rubber, Green
- * Shield: Metal
- * Nut: Metal
- * O-Ring: Rubber, Black
- * For panel thickness max: 4.5mm
- *  The Nut Is Packed Separately In The Bag

UNIT: mm				TITLE N SEN, M12 A -SHLD, SCREW RECEPTACLE, F, F, PCB S		ITEM NO		DRAWN BY Vicky		DATE 2025-10-27			
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±		SCALE 2:1		SIZE A4		SHEET 1 OF 2		DWG NO MSAS-XXPFFP-SF8001		CHECKED BY Ruru		DATE 2025-10-27	
		REV. J		WC-REV. A.5		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Rita		DATE 2025-10-27	

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

