





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

	1	2	3	4	5	6	7	8
F								
E								
D								
C								
B								
A								



- Note:
- * RoHS Compliant
 - * Important Dimension
 - * Waterproof rate: IP67, mated Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - Spring: Metal
 - * Shield: Metal
 - * Nut: Metal
 - * O-Ring: Rubber, Gray
 - * Gasket: Rubber, Black
 - * For Panel Thickness Max 2.8mm
 - * Recommend pcb thickness: 1.6mm
 - * The Gasket And Nut Are Packed Separately In The Bag

UNIT:mm						TITLE N SEN, M12 X -SHLD, RECEPTACLE, F, F, PCB S			ITEM NO			DRAWN BY Vicky		DATE 2025-11-05	
TOLERANCE		SCALE 3:2		SIZE A4		SHEET 2 OF 2		DWG NO MSXS-XXPFFP-SH7003			CHECKED BY Ruru		DATE 2025-11-05		
.X ±0.25		REV. G		WC-REV. A.1		QC:Inspection item		CUSTOMER ALTW			APPROVED BY Rita		DATE 2025-11-05		
.XX ±0.1															
.XXX ±0.05															
ANGLES ±1°															

Amphenol LTW
安費諾亮泰企業股份有限公司