



SIGN	DATE	DESCRIPTION	APPROVER
△	04/18`14	change the dimensional tolerance	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Contact Solder pin : Brass(CuZn) ,Tin plated
- Insulator (housing) : Thermoplastic (UL94V-0)

Electrical UL

- Voltage rating: 300V
- Current rating: 10A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:
- Critical dimension: ▽




N = Number of poles

Dim L=Nx5.75

Dim B=(N-1)x5.75

PART NO.	Tolerance
OP028U000001G	±0.10




P.C.B. LAYOUT

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		OP 5.75 Series Dim A=4.0mm (L=25.1mm,φ1.00) (Pin 尖為圓型)					
PART NO.				DWG NO.		80P0740	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
		Chen Bo	Chen Bo			X.	±0.50
		04/18`14	11/02`13			X.X	±0.30
						X.XX	±0.10
SHEET: 01/01		REV.: C				X°	±1°