


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C191395	2019/07/29	JC Chen	Dimensional tolerance change
C	C251579	2025/12/08	Vicky	 X5



RCP5SM-RCP5SM-TR7BXX

```

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
.
.
.
99 : 99Meters

```

Cable Length(L):01~99Meters

Shield	Drain Wire	Shield
8	Brown 棕	8
7	White/Brown 白/棕	7
6	Green 綠	6
5	White/Blue 白/藍	5
4	Blue 藍	4
3	White/Green 白/綠	3
2	Orange 橘	2
1	White/Orange 白/橘	1
Conn.1	Wire Color	Conn.2

Pin Out

UNIT: mm			TITLE RJ, C PLASTIC, C5E SHLD, M C PLASTIC, C5E SHLD, M		
TOLERANCE	$\pm 0.5\text{mm}$		SCALE	SIZE	SHEET OF
			4:5	A4	1 OF 1
			REV.	WC-REV.	QC: Inspection item
			C	A.2	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Vicky	2025-12-08
DWG NO	CHECKED BY	DATE
RCP5SM-RCP5SM-TR7BXX	Ruru	2025-12-08
CUSTOMER	APPROVED BY	DATE
ALTW	Rita	2025-12-08

△ Note:

- * RoHS Compliant
- * QC Important dimension
- * Waterproof rate: IP67, mated
- * Connector
 - Plug: PC, Gold Plated, Shielded
 - Gasket: Rubber, Black
 - Nut: Thermoplastic, Black
 - Outer mold: Thermoplastic, Black
- * Cable: CAT.5E FTP, 24#*4P+M+D+AL/MY, OD=6.5mm, PVC Jacket, Black
- * Cable Length Tolerance:
 - 01M: ±40mm
 - 02~05M: ±60mm
 - 06~10M: ±100mm
 - 11~30M: ±200mm
 - 30~99M: ±500mm