







	2	3	4	5	6	7	8																					
				<table><tr><th>REV.</th><th>ECN NO.</th><th>DATE</th><th>SIGN</th><th>DESCRIPTION</th></tr><tr><td>A</td><td></td><td>2022-10-26</td><td>Yuwei Chou</td><td>Change Rev.04 To Rev.A</td></tr><tr><td>B</td><td>C221764</td><td>2022-11-02</td><td>Yuwei Chou</td><td>△B*2</td></tr><tr><td>C</td><td>C251664</td><td>2025-12-19</td><td>JC Chen</td><td>△C*1</td></tr></table>		REV.	ECN NO.	DATE	SIGN	DESCRIPTION	A		2022-10-26	Yuwei Chou	Change Rev.04 To Rev.A	B	C221764	2022-11-02	Yuwei Chou	△B*2	C	C251664	2025-12-19	JC Chen	△C*1			
REV.	ECN NO.	DATE	SIGN	DESCRIPTION																								
A		2022-10-26	Yuwei Chou	Change Rev.04 To Rev.A																								
B	C221764	2022-11-02	Yuwei Chou	△B*2																								
C	C251664	2025-12-19	JC Chen	△C*1																								
																												
	SM8-XXPFFS-SF8001 XX: No. Of Pin																											
				Note: *  Important Dimension. * Waterproof Rate: IP68, Unmated 1m/24h. * Housing: Thermoplastic, Black. * Female Pin: Copper Alloy, Gold Plated. * Shell: Metal. * Screw Nut: Metal. * Panel O-Ring: Rubber, Green. * Housing O-Ring: Rubber, Green. * For panel thickness: 2.0~4.5mm. * Nut is packed separately in pe bag.																								
	UNIT:mm TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°			TITLE N SEN, SM8-STAINLESS, SCREW RECEPTACLE, F, F, SOLDER SCALE Free SIZE A4 SHEET 1 OF 1 REV. C WC-REV. A.1 :Inspection item		Amphenol LTW 安費諾亮泰企業股份有限公司																						
	ITEM NO DWG NO CUSTOMER		DRAWN BY JC Chen CHECKED BY Nan Su APPROVED BY Jerry		DATE 2025-12-19 DATE 2025-12-19 DATE 2025-12-19																							
	ALTW																											