

PATCH PANELS

C-HDM-3RUEN

HDM Enclosed Series 3RU Rackmount Panel Modular Fiber Chassis Supporting up to Twelve HDM Cassettes or Adapter Plates

DESCRIPTION

This HDM enclosed series 3RU rackmount panel is engineered for the most demanding fiber environments where maximum port density, protection, and cable organization are required. The 3RU enclosure supports up to twelve HDM cassettes or adapter plates, enabling flexible connector configurations and extremely high port counts. When fully populated and with the center cable management panel removed, the system supports up to 576 LC ports in 3RU, maximizing rack efficiency in high-density cross-connect and patching environments. An integrated center-RU cable management panel is included to improve fiber routing and bend-radius control. This panel can be removed when additional cassette capacity is required, giving operators the flexibility to prioritize either cable organization or maximum density.



FEATURES

- High Density, up to 576 LC ports in 3 RU(With cable management removed)
- Modular Patch Panel and Shuffle system
- Ability to utilize multiple connector types
- Enclosed design for maximum support and protection
- Removable panels for easy access
- An integrated center-RU cable management panel is optional to improve fiber routing and bend-radius control

APPLICATIONS

- Fiber breakout and patching
- Various connector types
- High density applications

Patch Panels Specifications

Rack Mountable	Yes - 19" Frames
Rack Height	3U
Cassette/Adapter Plate Capacity	12
Cassette/Adapter Plate Form Factor	HDM
Material	Steel
Material Finish	Black Powder Coat
Product Dimensions (inches)	5.25 in. x 19 in. x 20.5 in.
UNSPSC Code	43222821
Country Of Origin	China
RoHS Compliant	Yes