


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C221563	2022/09/28	Ruru	 X9



△ Note:



- * RoHS Compliant
- *  Important dimension
- * Waterproof rate: IPX6, mated
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - O-Ring: Rubber, Gray
 - Nut: Thermoplastic, Black
 - Outer mold: Thermoplastic, Black
- * Cable: UL2464, PVC Jacket, Black
- * Cable length tolerance: 1M: +50/-0 mm

1M < L ≤ 3M: +100/-0 mm
3M < L ≤ 5M: +150/-0 mm
5M < L ≤ 10M: ±100 mm
10M < L ≤ 20M: ±200 mm
20M < L ≤ 30M: ±300 mm
30M < L ≤ 99M: ±500 mm

UNIT : mm		TITLE N CERES, ME, C-10A, CABLE W/O SR F, M, MOLDING, SCREW 		
TOLERANCE ± 0.5		SCALE 1 : 1	SIZE A4	SHEET 1 OF 2
		REV. B	WC-REV. A.2	QC : Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO		DRAWN BY Tony_leng		DATE 2013-11-01	
DWG. NO  ICB-XXBFMM-SL6AXX		CHECKED BY Ruru		DATE 2013-11-01	
CUSTOMER ALTW		APPROVED BY Jerry		DATE 2013-11-01	

	1	2	3	4	5	6	7	8	THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.		
							5P	6.0		20	ICB-05BFMM-SL6AXX
							4P	5.5		20	ICB-04BFMM-SL6AXX
							Contacts	Cable OD		AWG	Item No.
F											
	ICB-XXBFMM-SL6AXX XX: No. Of Pin XX: 01~99Meters 01: 01Meter 02: 02Meters : 99: 99Meters										
E											
D											
C	Pin Out	4 3 2 1	White Black Blue Brown	白 黑 藍 棕	5 4 3 2 1	Green White Black Blue Brown	綠 白 黑 藍 棕				
			Pin #	Wire		Pin #	Wire				
B	Conn.										
		4P			5P						
	Pin Assignments Front View										
A	UNIT:mm		TITLE N CERES, ME, C-10A, CABLE W/O SR F, M, MOLDING, SCREW			Amphenol LTW		ITEM NO		DRAWN BY	DATE
	TOLERANCE		±0.5		SCALE 1:1		SIZE A4	SHEET 2 OF 2	DWG NO ICB-XXBFMM-SL6AXX	CHECKED BY Ruru	DATE 2013-11-01
			REV. B		WC-REV. A.2		QC: Inspection item		CUSTOMER ALTW	APPROVED BY Jerry	DATE 2013-11-01
	1	2	3	4	5	6	7	8	W10814-03-0001A2		