


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C221563	2022/09/28	Ruru	X6



Pin Out	3 2 1	Black Blue Brown	黑 藍 棕
	Pin #	Wire	
Conn.	 3P		

XX: No. Of Pin

ICC-XXBFMM-LL6AXX

XX: 01~99Meters
01: 01Meter
02: 02Meters
:
99: 99Meters

- Note:
- * RoHS Compliant
 - * Important dimension
 - * Waterproof rate: IPX6, mated
 - * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - O-Ring: Rubber, Gray
 - Nut: Thermoplastic, Black
 - Outer mold: Thermoplastic, Black
 - * Cable: UL2464, 16#*3C+D+Al/My, OD=7.5mm, PVC Jacket, Black
 - * Cable length tolerance: 1M: +50/-0 mm
1M < L ≤ 3M: +100/-0 mm
3M < L ≤ 5M: +150/-0 mm
5M < L ≤ 10M: ±100 mm
10M < L ≤ 20M: ±200 mm
20M < L ≤ 30M: ±300 mm
30M < L ≤ 99M: ±500 mm

UNIT:mm			TITLE N CERES, ME, C-20A, CABLE W/O SR F, M, MOLDING, 2LOCK	ITEM NO	DRAWN BY Tony_leng	DATE 2013-11-01
TOLERANCE ±0.5	SCALE 1:1			DWG NO ICC-XXBFMM-LL6AXX	CHECKED BY Ruru	DATE 2013-11-01
	REV. B	SIZE A4	SHEET 1 OF 1	CUSTOMER ALTW	APPROVED BY Jerry	DATE 2013-11-01
		WC-REV. A.2	: Inspection item			

Amphenol LTW
安費諾亮泰企業股份有限公司