

	1	2	3	4	5	6	7	8	
F					REV.	ECN NO.	DATE	SIGN	DESCRIPTION
					B	C221563	2022/10/03	Ruru	X5
E									
D									
C									
B									
A									

Pin Out

3	Black	黑
2	Blue	藍
1	Brown	棕

Pin # Wire

Conn.

3P

Pin Assignments Front View

ICC-XXBFMM-SL6AXX

XX: No. Of Pin

XX: 01~99Meters
01: 01Meter
02: 02Meters
:
99: 99Meters

Note:

- * RoHS Compliant
- * Important dimension
- * Waterproof rate: IPX6, mated
- * Connector
- Housing: Thermoplastic, Black
- Pin: Copper alloy, Gold plated
- O-Ring: Rubber, Gray
- Nut: Thermoplastic, Black
- Outer mold: Thermoplastic, Black
- * Cable: UL2464, 16#*3C+D+Al/My, OD=7.5mm, PVC Jacket, Black
- * Cable length tolerance: 1M: +50/-0 mm
1M < L ≤ 3M: +100/-0 mm
3M < L ≤ 5M: +150/-0 mm
5M < L ≤ 10M: ±100 mm
10M < L ≤ 20M: ±200 mm
20M < L ≤ 30M: ±300 mm
30M < L ≤ 99M: ±500 mm

UNIT:mm				TITLE N CERES, ME, C-20A, CABLE W/O SR F, M, MOLDING, SCREW		ITEM NO		DRAWN BY Tony_leng		DATE 2013-11-01			
TOLERANCE ±0.5		SCALE 1:1		SIZE A4		SHEET 1 OF 1		DWG. NO ICC-XXBFMM-SL6AXX		CHECKED BY Ruru		DATE 2013-11-01	
REV. B		WC-REV. A.2		Inspection item		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2013-11-01			

Amphenol LTW

安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

W10814-03-01A2