




	1	2	3	4	5	6	7	8		
F					REV.	ECN NO.	DATE	SIGN	DESCRIPTION	
					B	C210213	2021/04/22	Ruru	 X4	
					C	C221871	2022/12/02	Vicky	 X1	
E										
D										
C	Pin Out	5 4 3 2 1	Yellow Orange Red Brown Black	黄 橘 紅 棕 黑	 8HP-XXAFFM-SL7AXX XX: No. Of Pin XX:01~99Meters 01:01Meter 02:02Meters : 99:99Meters Note: * RoHS Compliant *  Important dimension  * Waterproof rate: IP67, mated Connector Housing: Thermoplastic, Black Pin: Copper alloy, Gold plated O-Ring: Rubber, Green Nut: Thermoplastic, Black Outer mold: Thermoplastic, Black * Cable: UL2464, 24#*5C, OD=5.0mm, PVC Jacket, Black * Cable length tolerance: 1M: +50/-0 mm 1M < L ≤ 3M: +100/-0 mm 3M < L ≤ 5M: +150/-0 mm 5M < L ≤ 10M: ±100 mm 10M < L ≤ 20M: ±200 mm 20M < L ≤ 30M: ±300 mm 30M < L ≤ 99M: ±500 mm					
		Pin #	Wire							
B	Conn.									
A	Pin Assignments Front View									
	UNIT:mm				TITLE O SEN, M8 W/KEY HY-PLASTIC CABLE W/SR, F, F, MOLDING 			ITEM NO	DRAWN BY	DATE
	TOLERANCE ±0.5 mm			SCALE 2:1	SIZE A4	SHEET 1	OF 1	DWG NO  8HP-XXAFFM-SL7AXX	CHECKED BY Jimmy	DATE 2014-02-22
			REV. C	WC-REV. A.2	 :Inspection item		CUSTOMER ALTW	APPROVED BY Jerry	DATE 2014-02-22	
	1	2	3	4	5	6	7	8		

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.