




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C210213	2021/04/22	Ruru	$\triangle B$ X4
C	C221871	2022/12/02	Vicky	$\triangle C$ XI




$\triangle B$
8HP-XXAMMM-SR7AXX
XX: No. Of Pin
XX: 01~99Meters
01: 01Meter
02: 02Meters
:
99: 99Meters

Pin Out	5	Yellow	黃
	4	Orange	橘
	3	Red	紅
	2	Brown	棕
	1	Black	黑
Pin #		Wire	
Conn.			
	5P		

Pin Assignments Front View

Note: $\triangle B$
* RoHS Compliant
* $\triangle C$ Important dimension
* Waterproof rate: IP67, mated
* Connector
Housing: Thermoplastic, Black
Pin: Copper alloy, Gold plated
Nut: Thermoplastic, Black
Outer mold: Thermoplastic, Black
* Cable: UL2464, 24#*5C, OD=5.0mm, PVC Jacket, Black
* Cable length tolerance: 1M: +50/-0 mm
1M < L ≤ 3M: +100/-0 mm
3M < L ≤ 5M: +150/-0 mm
5M < L ≤ 10M: ±100 mm
10M < L ≤ 20M: ±200 mm
20M < L ≤ 30M: ±300 mm
30M < L ≤ 99M: ±500 mm



UNIT:mm				TITLE O SEN, M8 W/KEY HY-PLASTIC CABLE W/SR, M, M, MOLDING $\triangle B$	
TOLERANCE		SCALE 9:5		SIZE A4	SHEET 1 OF 1
±0.5 mm		REV. C	WC-REV. A.4	$\triangle C$: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO		DRAWN BY Mila		DATE 2014-03-04	
DWG. NO $\triangle B$ 8HP-XXAMMM-SR7AXX		CHECKED BY Jimmy		DATE 2014-03-04	
CUSTOMER ALTW		APPROVED BY Jerry		DATE 2014-03-04	