


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C210213	2021/04/22	Ruru	$\triangle B$ X4
C	C221870	2022/12/02	Vicky	$\triangle C$ X1



Pin Out	5 4 3 2 1	Yellow Orange Red Brown Black	黃 橘 紅 棕 黑
	Pin #	Wire	
Conn.	 5P		

$\triangle B$
8H-XXAFFM-SL7AXX
XX: No. Of Pin
XX: 01~99Meters
01: 01Meter
02: 02Meters
:
99: 99Meters

Note: $\triangle B$
* RoHS Compliant
* ϕ Important dimension
 $\triangle C$ * Waterproof rate: IP67, mated
* Connector
Housing: Thermoplastic, Black
Pin: Copper alloy, Gold plated
O-Ring: Rubber, Green
Nut: Metal
Outer mold: Thermoplastic, Black
* Cable: UL2464, 24#5C, OD=5.0mm, PVC Jacket, Black
* Cable length tolerance: 1M: +50/-0 mm
1M < L ≤ 3M: +100/-0 mm
3M < L ≤ 5M: +150/-0 mm
5M < L ≤ 10M: ±100 mm
10M < L ≤ 20M: ±200 mm
20M < L ≤ 30M: ±300 mm
30M < L ≤ 99M: ±500 mm

UNIT:mm		TITLE O SEN, M8 W/KEY HY CABLE W/SR, F, F, MOLDING $\triangle B$		ITEM NO		DRAWN BY Mila	DATE 2014-02-21
TOLERANCE		SCALE 2:1	SIZE A4	SHEET 1	OF 1	CHECKED BY Jimmy	DATE 2014-02-21
±0.5 mm		REV. C	WC-REV. A.2	ϕ : Inspection item		APPROVED BY Jerry	DATE 2014-02-21
				CUSTOMER ALTW			
						8 W10814-03-0001A2	

Amphenol LTW
安費諾亮泰企業股份有限公司