




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C210213	2021/04/22	Ruru	 X4
C	C221870	2022/12/02	Vicky	 XI




 8H-XXAFFM-SR7AXX
XX: No. Of Pin
 XX: 01~99Meters
01: 01Meter
02: 02Meters
:
99: 99Meters

Pin Out	5	Yellow	黃
	4	Orange	橘
	3	Red	紅
	2	Brown	棕
	1	Black	黑
	Pin #	Wire	

Conn.	
	5P

Pin Assignments Front View



Conn.

Note: 
* RoHS Compliant
*  Important dimension
*  Waterproof rate: IP67, mated
* Connector
Housing: Thermoplastic, Black
Pin: Copper alloy, Gold plated
O-Ring: Rubber, Green
Nut: Metal
Outer mold: Thermoplastic, Black
* Cable: UL2464, 24#*5C, OD=5.0mm, PVC Jacket, Black
* Cable length tolerance: 1M: +50/-0 mm
1M < L ≤ 3M: +100/-0 mm
3M < L ≤ 5M: +150/-0 mm
5M < L ≤ 10M: ±100 mm
10M < L ≤ 20M: ±200 mm
20M < L ≤ 30M: ±300 mm
30M < L ≤ 99M: ±500 mm

UNIT:mm			TITLE O SEN, M8 W/KEY HY CABLE W/SR, F, F, MOLDING 		
TOLERANCE			SCALE 2:1	SIZE A4	SHEET 1 OF 1
±0.5 mm			REV. C	WC-REV. A.3	 : Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Mila	DATE 2014-02-22
DWG NO  8H-XXAFFM-SR7AXX	CHECKED BY Jimmy	DATE 2014-02-22
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2014-02-22