








REV.	ECN NO.	DATE	SIGN	DESCRIPTION
D	C192160	2019/12/21	Peng	 X1
E	C210686	2021/05/11	Vicky	 X5
F	C221882	2022/12/16	Vicky	 X1

Recommended
Panel Cut-Out
8-XXPMMS-SF7002

XX: No. Of Pin



3P




4P

 Pin Assignments Front View

Note:

- * RoHS Compliant
- *  Important dimension
-  * Waterproof rate: IP67, unmated
- * Connector
- Housing: Thermoplastic, Black
- Pin: Copper alloy, Gold plated
- * Shield: Metal
-  * Nut: Metal
- * O-Ring: Rubber, Black
-  * For panel thickness(screw type)max: 1.9mm
- * For panel thickness(snap-in type)max: 3.0mm
- * Nut is packed separately in pe bag

UNIT:mm



TITLE

O SEN, M8
RECEPTACLE, M, M, SOLDER

TOLERANCE

.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

SCALE

7:2

SIZE

A4

SHEET

1

OF

1

REV.

F

WC-REV.

A.6

 Inspection item**Amphenol LTW**

安費諾亮泰企業股份有限公司

ITEM NO

DWG NO

 8-XXPMMS-SF7002

CUSTOMER

ALTW

DRAWN BY

Ivan Lin

CHECKED BY

Tommy Hom

APPROVED BY

Luke Chang

DATE

2009-01-07

DATE

2009-01-07

DATE

2009-01-07