



Conn.



1 ACD-XXAFMM-SL7000
Color: Black



Contacts	Cable Jacket	Cable OD	AWG	Item No.
9P	PVC	6.0	24	ACD-09AFMM-SL7AXX
8P		5.5		ACD-08AFMM-SL7AXX
7P		5.8		ACD-07AFMM-SL7AXX


9	Black 黑	8	Green 綠	7	Green 綠
8	Red 紅	7	Yellow 黃	6	White 白
7	Pink 粉紅	6	Orange 橙	5	Brown 棕
6	Gray 灰	5	Red 紅	4	Red 紅
5	Yellow 黃	4	Blue 藍	3	Yellow 黃
4	Green 綠	3	White 白	2	Orange 橙
3	White 白	2	Brown 棕	1	Blue 藍
2	Blue 藍	1	Black 黑		
1	Brown 棕				

Pin # Wire


Pin # Wire

Pin # Wire


Pin Out



9 Pin



8 Pin



7 Pin

Pin Assignments Front View

ACD-XXAFMM-SL7AXX

07: 7Pin

09: 9Pin

XX: 01~99Meters

01: 01Meter

02: 02Meters

XX: 99Meters

Cable Length(L): 01~99Meters

Note:

- * $\varnothing$ Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Screw Nut: Nylon+GF, Black
- * Cable: UL2464 24AWG+Drain+Al/My
- * Cable Length Tolerance: 01M: 40mm
- 02M~05M: ± 60 mm
- 06M~10M: ± 100 mm
- 11M~30M: ± 200 mm
- 31M~99M: ± 500 mm

UNIT:mm
TOLERANCE
 ± 0.5

TITLE MIDDLE CABLE SCREW F CONN M PIN			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. A	WC-REV. A.1	$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Jinhai	DATE 2015-07-16
DWG NO ACD-XXAFMM-SL7AXX	CHECKED BY Rensong	DATE 2015-07-16
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2015-07-16