



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	LEN1610196~199	2015/12/07	Ruru	Change Logo & Note
D	LEN1790390~393	2017/09/27	Ruru	Update View
E	C190502	2019/04/02	Fu	Change 藍色 To 黑色



Note:



- * Important Dimensions.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Nut: Nylon+GF, Black
- * Gasket: EPDM, Black
- * Cable: UL2464 20AWG*3C+Drain+Al/My, UV Resistant, OD=5.0, Black
- * Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm
- * Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm
- * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

3	Yellow 黃色
2	White 白色
1	Black 黑色
Conn	Wire Color
Pin Out	


BB-03PMMM-SL7AXX

XX: 01~99Meter
01: 01Meter
02: 02Meters
:
99: 99Meters

Cable Length(L): 01~99Meters



Pin Assignments
Front View



Recommended Panel Cut-Out

UNIT:mm		TOLERANCE		TITLE	
±0.5 mm		Standard,Cable Screw 3Pin M Conn. M Pin		SCALE	
				1:1	
				SIZE	
				A4	
				SHEET	
				1	
				OF	
				1	
				REV.	
				E	
				WC-REV.	
				.0	
				Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	BB-03PMMM-SL7AXX	DRAWN BY	Fu	DATE	2019-04-02
DWG NO	BB-03PMMM-SL7AXX	CHECKED BY	Feng li	DATE	2019-04-02
CUSTOMER	ALTW	APPROVED BY	Jerry	DATE	2019-04-02