


1		2		3		4		5		6		7		8	
								REV.	ECN NO.	DATE	SIGN	DESCRIPTION			
								B	LEN1540297	2015/04/16	Micky	Modify #2 Wire Colore			
								C	C220458	2022/04/01	Ruru	△C X8			
								D	C230120	2023/02/03	Ruru	△D X1			

</

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1540297	2015/04/16	Micky	Modify #2 Wire Colore
C	C220458	2022/04/01	Ruru	△C X8
D	C230120	2023/02/03	Ruru	△D X1



- Note: △C
- * RoHS Compliant
 - * ∅ Important dimension
 - △* Waterproof rate: IP68, mated 1m/24h
 - * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper Alloy, Gold Plated
 - O-Ring: Rubber, Dark Gray
 - Nut: Thermoplastic, Black
 - Outer mold: Thermoplastic, Black
 - * Cable: UL21388, PVC Jacket, Black
 - * Cable length tolerance: 1M: +50/-0 mm
 - 1M < L ≤ 3M: +100/-0 mm
 - 3M < L ≤ 5M: +150/-0 mm
 - 5M < L ≤ 10M: ±100 mm
 - 10M < L ≤ 20M: ±200 mm
 - 20M < L ≤ 30M: ±300 mm
 - 30M < L ≤ 99M: ±500 mm

UNIT:mm				TITLE XLOK, B-10A, CABLE W/SR F, M, MOLDING, PUSH LOCK △C				ITEM NO		DRAWN BY Micky		DATE 2014-09-12	
TOLERANCE		±0.5 mm		SCALE 3:2	SIZE A4	SHEET 1	OF 2	DWG NO BB-XXAFMM-QL8DXX △C		CHECKED BY Spring		DATE 2014-09-12	
REV. D		WC-REV. A.2		∅: Inspection item				CUSTOMER ALTW		APPROVED BY Kevin		DATE 2014-09-12	

Amphenol LTW
安費諾亮泰企業股份有限公司

	1	2	3	4	5	6	7	8												
F						△	<table><tr><td>3P</td><td rowspan="2">PVC</td><td>6.5</td><td rowspan="2">16</td><td>BB-03AFMM-QL8DXX</td></tr><tr><td>2P</td><td>6.0</td><td>BB-02AFMM-QL8DXX</td></tr><tr><td>Contacts</td><td>Cable Jacket</td><td>Cable OD</td><td>AWG</td><td>Item No.</td></tr></table>	3P	PVC	6.5	16	BB-03AFMM-QL8DXX	2P	6.0	BB-02AFMM-QL8DXX	Contacts	Cable Jacket	Cable OD	AWG	Item No.
	3P	PVC	6.5	16	BB-03AFMM-QL8DXX															
	2P		6.0		BB-02AFMM-QL8DXX															
Contacts	Cable Jacket	Cable OD	AWG	Item No.																
E																				
D																				
C																				
B																				
A																				

△

BB-XXAFMM-QL8DXX

XX: No. Of Pin

XX

: 01~99Meters

01

: 01Meter



02

: 02Meters
:
:


99

: 99Meters

△

Pin Out	2 1	Red Black	紅 黑	△	3 2 1	Red Brown Black	紅 棕 黑
	Pin #	Wire			Pin #	Wire	
Conn.							
	2P				3P		

Pin Assignments Front View

UNIT:mm		TITLE	XLOK, B-10A, CABLE W/SR F, M, MOLDING, PUSH LOCK △		ITEM NO	DRAWN BY	DATE
TOLERANCE		SCALE	SIZE	SHEET	DWG NO	CHECKED BY	DATE
±0.5 mm		3:2	A4	2 OF 2	BB-XXAFMM-QL8DXX △	Spring	2014-09-12
		REV.	WC-REV.	QC	CUSTOMER	APPROVED BY	DATE
		D	A.2	Inspection item	ALTW	Kevin	2014-09-12

Amphenol LTW

安費諾亮泰企業股份有限公司

6	7	8
		W10814-03-0001A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.