




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C191730	2019/10/08	Vicky	Update Code & Wire Tolerance
C	C220377	2022/03/07	Ruru	$\triangle C$ X5


$\triangle C$
CBD-XXRFFC-RC8CXX
XX: No. Of Pin (Pin數)

$\frac{10}{15/20}$: 100mm
: 150mm
: 200mm


$\triangle B$ A0 : 1000mm
Cable Pitch Unit: 50mm
Wire Length(L): 100~1000mm



Conn.




Recommended
Panel Cut-out



Conn.
Pin Assignments
Front View

6	Black (20AWG)	黑
5	White (20AWG)	白
4	Green (20AWG)	綠
3	Blue (16AWG)	藍
2	Red (16AWG)	紅
1	Black (16AWG)	黑
Conn.	Wire Color	

Pin Out



- $\triangle C$ Note:
- * QC Important Dimension
 - * Waterproof Rate: IP68
 - * Connector: Thermoplastic, Black
 - * Female Pin: Copper Alloy, Gold Plated
 - * Gasket: Rubber, Gray
 - * Nut: Thermoplastic, Black
 - * Wire Harness: UL1015
 - * Panel Thickness Max: 5.0mm
 - * Recommended Nut Torque: 8~10 kgf.cm
 - * Wire Harness Tolerance: 100 ± 10mm
101~300mm ± 15mm
301~1000mm ± 20mm
 - * Prohibiting the use of place in oils

UNIT:mm
TOLERANCE
 $\pm 0.5\text{mm}$

TITLE
RBL, C-10A+5A, REAR FASTENED
F, F, CRIMP, RBL
SCALE
1:1
REV.
C
SIZE
A4
WC-REV.
.0
SHEET
1
OF
1
 QC : Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Peng	DATE 2019-05-10
DWG NO CBD-XXRFFC-RC8CXX $\triangle C$	CHECKED BY Mafei	DATE 2019-05-10
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2019-05-10