


1	2	3	4
---	---	---	---



CD-XXAFFM-RL8EXX

XX: No. Of Pin


```

—XX:01~99Meters
01:01Meter
02:02Meters
:
99:99Meters

```

Note: $\triangle B$

- * RoHS Compliant
- *  Important dimension
- * Waterproof rate: IP68, mated 1m/24h
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper Alloy, Gold Plated
 - O-Ring: Rubber, Gray
 - Outer mold: Thermoplastic, Black
- * Cable: SJTW, 18#*3C, OD=8.0mm, PVC Jacket, Black
- * Cable length tolerance: 1M: +50/-0 mm
 - 1M < L ≤ 3M: +100/-0 mm
 - 3M < L ≤ 5M: +150/-0 mm
 - 5M < L ≤ 10M: ±100 mm
 - 10M < L ≤ 20M: ±200 mm
 - 20M < L ≤ 30M: ±300 mm
 - 30M < L ≤ 99M: ±500 mm
- * Prohibiting the use of place in oils

Pin Out	4 Green 緑 3 White 白 1 Black 黒
Pin Assignments Front View	 3Pin

UNIT: mm			TITLE			RBL, C-5A, CABLE W/SR F, F, MOLDING, RBL			
TOLERANCE			SCALE	SIZE	SHEET		OF		
± 0.5			3:4	A4	1		1		
			REV. B	WC-REV. A.1	QC: Inspection item				

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Peng	DATE 2019-03-22
DWG NO B.CD-XXAFFM-RL8EXX	CHECKED BY Mafei	DATE 2019-03-22
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2019-03-22