






	1	2	3	4	5	6	7	8	
F					REV.	ECN NO.	DATE	SIGN	DESCRIPTION
					B	C230313	2023/03/15	Ruru	 X5
					C	C231210	2023/09/15	Vicky	 X1
E									
D					XX: No. Of Pin  CD-XXAMFM-RL8EXX XX: 01~99Meters 01: 01Meter 02: 02Meters : 99: 99Meters				
C					 Conn.				
B	Pin Out		4 Green 綠 3 White 白 1 Black 黑		Note:  * RoHS Compliant *  Important dimension * Waterproof rate: IP68, mated 1m/24h * Connector - Housing: Thermoplastic, Black - Pin: Copper Alloy, Gold Plated - Gasket: Rubber, Gray - O-Ring: Rubber, Gray - Outer mold: Thermoplastic, Black * Cable: SJTW, 18#*3C, OD=8.0mm, PVC Jacket, Black * Cable length tolerance: 1M: +50/-0 mm 1M < L ≤ 3M: +100/-0 mm 3M < L ≤ 5M: +150/-0 mm 5M < L ≤ 10M: ±100 mm 10M < L ≤ 20M: ±200 mm 20M < L ≤ 30M: ±300 mm 30M < L ≤ 99M: ±500 mm * Prohibiting the use of place in oils				
Pin Assignments Front View		 3P							
A	UNIT:mm			TITLE RBL, C-5A, CABLE W/SR M, F, MOLDING, RBL 		ITEM NO		DRAWN BY	DATE
TOLERANCE		±0.5		SCALE 3:4 SIZE A4 SHEET 1 OF 1		DWG NO  CD-XXAMFM-RL8EXX		CHECKED BY	DATE
				REV. C WC-REV. .0  Inspection item		CUSTOMER ALTW		APPROVED BY	DATE
								Peng	2019-03-22
								Mafei	2019-03-22
								Jerry	2019-03-22

Amphenol LTW
安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.