

PATCH PANELS

C-HDM-1RUOP

HDM Series 1RU Open Rackmount Panel Modular Fiber Chassis Supporting up to Four HDM Cassettes or Adapter Plates

DESCRIPTION

This HDM series 1RU open rackmount panel with support for up to 4 HDM cassettes or adapter plates, is a high-density modular fiber platform engineered for flexibility, accessibility, and efficient fiber management in space-constrained network environments. Designed for scalability, the HDM series enables seamless transitions between patching, cross-connect, and shuffle applications while maintaining high port density supporting up to 192 LC ports using 4 cassettes or adapter plates in 1RU when fully populated. The modular architecture ensures future-proof expansion as network demands evolve, making it ideal for data centers, central offices, and high-performance enterprise networks.



FEATURES

- High Density, up to 192 LC ports in 1 RU
- Modular Patch Panel and Shuffle system
- Ability to utilize multiple connector types
- Open design for easy access of full panel

APPLICATIONS

- Fiber breakout and patching
- Various connector types
- High density applications

Patch Panels Specifications

Rack Mountable	Yes - 19" Frames
Rack Height	1U
Cassette/Adapter Plate Capacity	4
Cassette/Adapter Plate Form Factor	HDM
Material	Steel
Material Finish	Black Powder Coat
Product Dimensions (inches)	1.7 in. x 19 in. x 14.4 in.
UNSPSC Code	43222821
Country Of Origin	China
RoHS Compliant	Yes