


C-HDM-24FLCAP-AQ

HDM Series 24-Port LC Adapter Plate for the HDM Rackmount Systems with Aqua Ports

DESCRIPTION

The HDM Series 24-Port adapter plate with 12 Duplex LC/UPC patch ports provides high-density duplex fiber connectivity in a compact, modular form factor optimized for the HDM rackmount platform. Designed for seamless compatibility with HDM rackmount panels, the adapter plate installs easily and can be swapped without disrupting adjacent ports or chassis hardware. As part of the broader HDM adapter plate and cassette ecosystem, it is fully interchangeable with MPO, LC, SC, and other connector types allowing mixed connector deployments within the same HDM enclosure. This adapter plate is ideal for data center, service provider, and enterprise environments that require high-density connectivity with modular flexibility and clean cable management.



FEATURES

- High Density, with 24 LC adaptors
- Fits HDM system rack mount panels
- Interchangeable with wide variety of connector types within HDM adapter plate and cassette family

APPLICATIONS

- Fiber breakout and patching
- Rapid Data Center Deployment
- High density applications

Adapters Plates Specifications

Form Factor	HDM
Connector Type	LC
Port Count	24
Fiber Count	24
Material	Steel
Material Finish	Black Powder Coat
Product Dimensions (inches)	1.67 in. x 4.15 in. x .06 in.
UNSPSC Code	43223337
Country Of Origin	China
RoHS Compliant	Yes