

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	E191618	2019/09/17	Ruru	Update Code & Wire Tolerance
C	C220419	2022/03/15	Vicky	△ X5

△ DCD-XXRFFC-RS8CXX

XX: No. Of Pin

10:100mm

15:150mm


20:200mm

f


△ A0:1000mm

Cable Pitch Unit=50mm

Wire Length (L):100~1000 mm




With Liquid Glue




Gasket

1 Connector

3 Screw



Wire Harness




△ Note:




- * ⌀ Important Dimension
- * Waterproof Rate: IP68(1M/24H)
- * Housing: Thermoplastic, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Gasket: Rubber, Gray
- * Wire Harness: UL1015 12AWG
UL1430 20AWG
- * Blind holes for the screws used M3X0.5mm
- * Blind Hole Size M3X0.5mm
- * Screw Torque: 1.5~2kgf.cm
- * Wire Harness Tolerance: 100mm ±10mm
101~300mm ±15mm
301~1000mm ±20mm
- * Prohibiting the use of place in oils

PE BAG

4 SETS



Blind-Hole

Effective Depth
of ThreadPin Assignments
Front ViewRecommended
Panel Cut-out

8	Black (20AWG)	黑
7	Yellow (20AWG)	黃
6	Orange (20AWG)	橙
5	White (20AWG)	白
4	Green (20AWG)	綠
3	Blue (12AWG)	藍
2	Red (12AWG)	紅
1	Black (12AWG)	黑
Conn.	Wire Color	
	Pin Out	

UNIT:mm	
TOLERANCE	±0.5mm

TITLE RBL, D-20A+5A, REAR FASTENED
F, F, CRIMP, RBL

SCALE	1:1	SIZE	A4	SHEET	1	OF	1
REV.	C	WC-REV.	.0	QC	Inspection item		

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DWG NO	CUSTOMER	DRAWN BY	CHECKED BY	APPROVED BY	DATE
	DCD-XXRFFC-RS8CXX△	ALTW	Ruru	Rita	Max	2019-09-17