




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
E	C220064	2022/01/13	Ouyang	△E x1
F	C220669	2022/05/05	Ouyang	△F x1
G	C251344	2025/10/21	Kea	△G x5

Note:
* RoHS Compliant
* ⌀ Important Dimension
△G * Waterproof Rate: IP68, mated 1m/24h
* Connector △E
Housing: Thermoplastic, Ecrú
Pin: Copper Alloy, Gold Plated
Internal O-Ring: Rubber, Black.
Outer O-Ring: Rubber, Red
* Shield: Metal
* Nut: Metal
* Use with waterproof cap or dust cap
Panel thickness Max: 5.0mm
* Use without waterproof cap or dust cap
Panel thickness max: 9.0mm
* O-Ring and nut are assembled on connectors

UNIT:mm	⌀ ⌀	TITLE	FLO 1K PANEL CONNECTOR
TOLERANCE	△G	SCALE	1:1
.X	±0.25	SIZE	A4
.XX	±0.1	SHEET	1 OF 2
.XXX	±0.05	REV.	G
ANGLES	±1°	WC-REV.	.0 ⌀ : Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO.	△B	DRAWN BY	Kea	DATE	2025/10/21
DWG NO.	FLKC-XXEGFS-XCP-XXX	CHECKED BY	Wen	DATE	2025/10/21
CUSTOMER	ALTW	APPROVED BY	Aric	DATE	2025/10/21

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

W10814-03-西製01A