




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

•
•
•

Cable Length(L):01~99Meters

$$\triangle F$$

- * RoHS Compliant
- *  Important Dimension To Check
- * Waterproof Rate: IP67, Mated 1M/30mins
- * Housing: Thermoplastic, Black
- * Gasket: Rubber, Black
- * Screw: Metal
- * Cable: UL2464 26AWG*44C+Drain+Al/My,
(UV Resistant) OD=10.5mm, Black



* Cable Length Tolerance: 1M: +50/-0 mm
1M<L≤3M: +100/-0mm
3M<L≤5M: +150/-0mm
5M<L≤10M: ±100mm
10M<L≤20M: ±200mm
20M<L≤30M: ±300mm
30M<L≤99M: ±500mm

Amphenol LTW

安費諾亮泰企業股份有限公司