





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



Note:

- * RoHS Compliant
- * Important Dimension
- * Waterproof rate: IP68, mated 1m/24h
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold/Tin plated
 - Extension Nut: Metal
 - O-Ring: Rubber, Black
- * Clamp Cage: Thermoplastic, Original
- * Sealing Nut: Metal
- * Seal For Cable:
 - Seal(Gray)+Seal(Gray): $\varnothing 5.8\text{mm} \sim \varnothing 7.1\text{mm}$
 - Seal(Gray)+Seal(Black): $\varnothing 4.7\text{mm} \sim \varnothing 5.7\text{mm}$
- * Applicable wire gauge: 20AWG~26AWG
- * One set unassembled in one pe bag

UNIT:mm



TOLERANCE
.X ± 0.25
.XX ± 0.1
.XXX ± 0.05
ANGLES $\pm 1^\circ$

TITLE
M12 A-SHLD, SCREW
CABLE W/O SR, F, F, FI IDC

SCALE 1:1
REV. D
SIZE A4
WC-REV. .0
SHEET 2 OF 3
 : Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Yunchen	DATE 2026/06/10
DWG NO MSAS-XXBFFD-SL8001	CHECKED BY Wen	DATE 2026/06/10
CUSTOMER ALTW	APPROVED BY Aric	DATE 2026/06/10

W10814-03-西製01A