

REV.

ECN NO.

DATE

SIGN

DESCRIPTION

D

LENI350142

2013/05/08

Lu Di

Change Logo

E

LE31730072

2017/03/02

Ruru

Change Outer Mold Design

F

C241496

2024/12/24

Ruru

F

XI

Conn.2

45°

Screw Nut

Connector

Inner Mold

Outer Mold

Color: Black

Wire Harness

12 ~ 3

56.8

44.7

Amphenol

D

E

Front View

Conn.3

45°

Back View

45°

Conn.1

Pin Assignments

Front View

Blue (24AWG)	藍	5	5	5
White (24AWG)	白	4	4	4
Black (22AWG)	黑	3	3	3
Red (22AWG)	紅	2	2	2
Green (24AWG)	綠	1	1	1
Wire Color		Conn.1	Conn.2	Conn.3

Pin Out

UNIT:mm

TOLERANCE

± 0.5mm

B

TITLE

M12 Conn T Adaptor

MMM Conn MMM Pin, 5Pin

C

SCALE

1:1

SIZE

A4

SHEET

1

OF

1

REV.

F

WC-REV.

A.1

QC

: Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

PS-050505-MMM-TS001

DWG NO

PS-050505-MMM-TS001

CUSTOMER

ALTW

DRAWN BY

Ruru

CHECKED BY

Rita

APPROVED BY

Fred

DATE

2024-12-24

DATE

2024-12-24

DATE

2024-12-24

Note:

*

 Important Dimension

*

 Waterproof Rate: IP68

*

 In 1 meter water within 24 hours

*

 Connector: Thermoplastic, Black

*

 Screw Nut: Thermoplastic, Black

*

 Pin: Copper Alloy, Gold Plated

C

*

 Wire Harness: UL1061 24AWG, Green, White, Blue

C

*

 Wire Harness: UL1061 22AWG, Red, Black

W10814-03-0001A2