




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C191337	2019/08/05	JC Chen	Dimensional tolerance change
C	C251489	2025/11/13	Ruru	 X5



Drain Wire	接地線	Shield
Brown	棕	8
White/Brown	白/棕	7
Green	綠	6
White/Blue	白/藍	5
Blue	藍	4
White/Green	白/綠	3
Orange	橘	2
White/Orange	白/橘	1
Wire Color		Plug
Pin Out		

```

RCP-5SBMMM-SLM7BXX
      |
      XX: 01~99Meters
      01: 01Meters
      02: 02Meters
      |
      99: 99Meters
Cable Length(L):01~99Meters

```

Note:

- *  Important Dimension
- * Waterproof Rate: IP67
- * Plug: 8P8C, Gold Plated, Shielded
- * Screw Nut: Nylon+GF, Black
- * Cable: CAT5E FTP 24#*4P+D
+Al/My(UV Resistant) OD=6.5mm, Black.
- * Cable Length Tolerance: 01M: $\pm 40\text{mm}$
02~05M: $\pm 60\text{mm}$
06~10M: $\pm 100\text{mm}$
11~30M: $\pm 200\text{mm}$
30~99M: $\pm 500\text{mm}$

UNIT:mm		 	TITLE RJ, C PLASTIC, C5E SHLD CABLE W/O SR, M, MOLDING, SCREW			Amphenol LTW		ITEM NO	DRAWN BY	DATE
TOLERANCE ± 0.5mm			SCALE 1:1	SIZE A4		SHEET 1 OF 1	安費諾亮泰企業股份有限公司	DWG NO RCP-5SBMMM-SLM7BXX	CHECKED BY Vicky	DATE 2025-11-13
			REV. C	WC-REV. A.3		QC: Inspection item		CUSTOMER ALTW	APPROVED BY Rita	DATE 2025-11-13