



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1440195	2014/05/10	Tom	Updated The Note
C	LEN1490327	2014-09-01	Tom	Change 94V0 Material
D	C241104	2024/09/26	Ruru	 X6

RDP-5SAMMM-SLM7BXX

```

—XX: 01~99Meter
01: 01Meter
02: 02Meters
    :
    :
99: 99Meters
Cable Length(L):01~99Meters

```

X:
(B)CAT5E FTP

Note:

- * **Ⓚ** Important Dimension To Check.
- * Waterproof Rate: IP67
- * Plug: PC, Gold Plated
- * Screw Nut: Thermoplastic, Black
- * Gasket: Rubber, Gray
- * Cable: CAT5E FTP, OD : $\varnothing 6.5$ Black
- * Cable Length Tolerance:
 - 01M: $\pm 40\text{mm}$
 - 02~05M: $\pm 60\text{mm}$
 - 06~10M: $\pm 100\text{mm}$
 - 11~30M: $\pm 200\text{mm}$
 - 30~99M: $\pm 500\text{mm}$

Drain Wire	接地	Shield			
Brown	棕	8	Twist 對絞		
White/Brown	白/棕	7			
Green	綠	6	Twist 對絞	Twist 對絞	
White/Blue	白/藍	5			
Blue	藍	4			
White/Green	白/綠	3	Twist 對絞		
Orange	橘	2			
White/Orange	白/橘	1			
Wire Color		Plug			
Pin Out					

UNIT: mm		TITLE RJ, D PLASTIC, C5E SHLD CABLE W/SR, M, MOLDING, SCREW 		
TOLERANCE	± 0.5	SCALE 1:1	SIZE A4	SHEET 1 OF 1
		REV. D	WC-REV. A.16	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Ruru	2024-09-26
DWG NO	CHECKED BY	DATE
RDP-5SAMMM-SLM7BXX	Rita	2024-09-26
CUSTOMER	APPROVED BY	DATE
ALTW	Fred	2024-09-26