





- * RoHS Compliant
- *  Important dimension
- * Waterproof rate: IP68, mated 1m/24h
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
-  Nut: Metal
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
-  Nut: Metal
- O-Ring: Rubber, Gray
- * Outer mold: Thermoplastic, Black
- * Cable: (22#*IP+AL)+(24#*IP+AL)+Drain+AL/My
+Braid, PVC UV Cable OD=7.1mm, Gray
- * Wire Harness: UL1007 22AWG
UL1007 24AWG
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Conn.2
Pin Assignment
Front View

5	Blue 藍(24AWG)	5	Blue 藍(24AWG)
4	White 白(24AWG)	4	White 白(24AWG)
3	Black 黒(22AWG)	3	Black 黒(22AWG)
2	Red 紅(22AWG)	2	Red 紅(22AWG)
1	Green 緑(22AWG)	1	Drain (22AWG)
Conn.1	Wire Harness	Conn.2	Cable
Pin Out			

 $\pm 0.5 \text{ mm}$

TITLE	ACC, NMEA, APVD, T ADA W/ CB ME
-------	------------------------------------

ection item

A 2

Amphenol LTW

安費諾亮泰企業股份有限公司

2026-06-16

2026-06-16

2026-06-16