

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C190403	2019/03/12	Vicky	Change Note
C	C220628	2022/05/11	Vicky	△C X4
D	C230119	2023/02/09	Vicky	△D X1


△C DC-XXRMFS-QC800P


XX: No. Of Pin





Recommended Panel Cut-Out













2P



3P



5P

Pin Assignments Front View

△B △C
Note:
* RoHS Compliant
* QC Important dimension
△D * Waterproof rate: IP68, unmated 1m/24h
* Connector
  Housing: Thermoplastic, Black
  Pin: Copper Alloy, Gold plated
* Nut: Thermoplastic, Black
* Gasket: Rubber, Gray
* For panel thickness max: 3.6mm
* Gasket and nut are packed separately in pe bag

UNIT: mm

TOLERANCE
.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE: XLOK, D-20A, REAR FASTENED M, F, SOLDER, PUSH LOCK △C

SCALE 3:2 | SIZE A4 | SHEET 1 OF 1

REV. D | WC-REV. A.3 | QC: Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY: Vicky	DATE: 2019-03-12
DWG NO: △C DC-XXRMFS-QC800P	CHECKED BY: Rita	DATE: 2019-03-12
CUSTOMER: ALTW	APPROVED BY: Max	DATE: 2019-03-12

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.