
PRODUCT DATASHEET



Soldered Protoboard

333399

Soldered Protoboard offers a permanent prototyping solution with easy-to-follow markings and durable copper pads for reliable connections.

Full product documentation, files and tutorials: **solde.red/333399**

CORE ATTRIBUTES

SKU **333399**

WEIGHT **10 g**

BARCODE **732388637201**

DESCRIPTION

Protoboard gives you a permanent alternative to a **breadboard**. Components solder directly onto copper pads arranged in rows and columns, so the connections stay in place instead of relying on spring contacts. Clear column and row markings make it easy to lay out parts and follow a schematic while soldering, and the board has a **solder mask** on one or both sides depending on size.

This listing is a pack of **3 boards** per size, available in **2×8cm**, **4×6cm**, **7×9cm**, and **8×12cm**, selectable from the size dropdown above.

Once a circuit works on a breadboard, moving it to a protoboard makes it permanent without designing a custom **PCB**. The pack suits small projects, one-off builds, or keeping spares on hand, since each size ships as three boards instead of one.

TECHNICAL DETAILS

- **Type:** Solderable protoboard (permanent prototyping board)
- **Pack quantity:** 3 boards per size
- **Available sizes:** 2×8cm, 4×6cm, 7×9cm, 8×12cm
- **Layout:** Copper pads in rows and columns with printed markings
- **Solder mask:** One or both sides, depending on size

LINKS

Full Documentation	`https://docs.soldered.com/protoboards/`

GALLERY

