

PRODUCT DATASHEET



Water Pump 12V

555087

This 12V water pump easily moves up to 240L of fluid per hour, reaching heights of 300cm for versatile liquid transfer.

Full product documentation, files and tutorials: solde.red/555087

CORE ATTRIBUTES

SKU 555087

WEIGHT 95 g

BARCODE 108643

DESCRIPTION

This water pump is extremely easy to use. Soak it in the water or liquid that you want to pump, add a tube to the drain and connect it to the power supply. You can also immerse the pump in the liquid you want to decant. In that case you don't need to attach a inlet tube in this case. It operates at 12V and is able to expel 240L of fluid per hour. • **Voltage:** 12V • **Max. height fluid can reach:** 300cm • **Flow rate:** 240L/h • **External diameter of drainage tube:** 8mm • **Pump dimensions:** 55 × 52 × 41 mm

TECHNICAL DETAILS

- **Voltage:** 12V
- **Max. height fluid can reach:** 300cm
- **Flow rate:** 240L/h
- **External diameter of drainage tube:** 8mm
- **Pump dimensions:** 55 × 52 × 41 mm / 2.2" x 2.1" x 1.6"

GALLERY

