



LOGO! contact 230 Switching module for direct switching of resistive loads up to 20 A and motors up to 4 kW, 230 V AC, 3 NO contacts+1 NC EAN: 4025515050759

Supply voltage			
Rated value (AC)		Yes	
• 230 V AC			
Line frequency			
• permissible range, lower limit		47 Hz	
• permissible range, upper limit		63 Hz	
Standards, approvals, certificates			
CE mark		Yes	
Ambient conditions			
Ambient temperature during operation			
• min.		-25 °C	
• max.		55 °C	
Dimensions			
Width		36 mm	
Height		72 mm	
Depth		55 mm	
Weights			
Weight, approx.		160 g	
Classifications			
		Version	Classification
	eClass	16	27-24-22-16
	eClass	14	27-24-22-16
	eClass	12	27-24-22-16
	eClass	9.1	27-24-22-16
	eClass	9	27-24-22-16
	eClass	8	27-24-22-16
	eClass	7.1	27-24-22-16
	eClass	6	27-24-22-16
	ETIM	10	EC001417
	ETIM	9	EC001417
	ETIM	8	EC001417
	ETIM	7	EC001417
	IDEA	4	3565
	UNSPSC	15	32-15-17-05
Approvals / Certificates			
General Product Approval		Maritime application	other



[Manufacturer Declaration](#)



[Confirmation](#)

last modified:

5/22/2024