

Siemens
EcoTech



SIMATIC ET 200SP, Analog input module, AI 8xI 2-/4-wire Basic, suitable for BU type A0, A1, Color code CC01, Module diagnostics, 16 bit

General information	
Product type designation	AI 8xI 2-/4-wire BA
HW functional status	FS23 or higher
Firmware version	V2.0.0
• FW update possible	Yes
usable BaseUnits	BU type A0, A1
Color code for module-specific color-coded label	CC01
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
• Measuring range scalable	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	TIA Portal V21
• STEP 7 configurable/integrated from version	V5.7 SP3
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.45
Operating mode	
• Oversampling	No
• MSI	No
CiR - Configuration in RUN	
Reparameterization possible in RUN	No
Calibration possible in RUN	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	25 mA
Current consumption, max.	725 mA
Encoder supply	
24 V encoder supply	
• 24 V	Yes
• Short-circuit protection	Yes
• Output current, max.	0.7 A; total current of all encoders/channels
Power loss	

Power loss, typ.	0.7 W
Address area	
Address space per module	
• Address space per module, max.	16 byte
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	
• 1-wire connection	BU type A0, A1
• 2-wire connection	BU type A0, A1
• 4-wire connection	BU type A0, A1 + potential distributor module
Analog inputs	
Number of analog inputs	8; Single-ended
• For current measurement	8
permissible input current for current input (destruction limit), max.	50 mA
Cycle time (all channels), min.	1 ms; per channel
Input ranges (rated values), currents	
• 0 to 20 mA	Yes
— Input resistance (0 to 20 mA)	100 Ω; 15 bit
• -20 mA to +20 mA	Yes
— Input resistance (-20 mA to +20 mA)	100 Ω; 16 bit incl. sign
• 4 mA to 20 mA	Yes
— Input resistance (4 mA to 20 mA)	100 Ω; 15 bit
Cable length	
• shielded, max.	200 m
Analog value generation for the inputs	
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Integration time, parameterizable	Yes
• Interference voltage suppression for interference frequency f1 in Hz	16.67 / 50 / 60 / 4 800 (16.67 / 50 / 60)
• Conversion time (per channel)	180 / 60 / 50 / 0.625 (67.5 / 22.5 / 18.75) ms
Smoothing of measured values	
• Number of smoothing levels	4
• Parameterizable	Yes
• Step: None	Yes
• Step: low	Yes; 4x smoothing
• Step: Medium	Yes; 8x smoothing
• Step: High	Yes; 16x smoothing
Encoder	
Connection of signal encoders	
• for voltage measurement	No
• for current measurement as 2-wire transducer	Yes
— Burden of 2-wire transmitter, max.	650 Ω
• for current measurement as 4-wire transducer	Yes
Errors/accuracies	
Linearity error (relative to input range), (+/-)	0.01 %
Temperature error (relative to input range), (+/-)	0.005 %/K
Crosstalk between the inputs, min.	50 dB
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.05 %
Operational error limit in overall temperature range	
• Current, relative to input range, (+/-)	0.5 %
Basic error limit (operational limit at 25 °C)	
• Current, relative to input range, (+/-)	0.3 %
Interference voltage suppression for $f = n \times (f1 \pm 1 \%)$, f1 = interference frequency	
• Series mode interference (peak value of interference < rated value of input range), min.	70 dB; With conversion time 67.5 / 22.5 / 18.75 ms: 40 dB

Interrupts/diagnostics/status information			
Diagnostics function		Yes	
Alarms			
• Diagnostic alarm		Yes	
• Limit value alarm		No	
Diagnoses			
• Monitoring the supply voltage		Yes	
• Wire break		Yes; at 4 to 20 mA	
• Short-circuit		Yes; Sensor supply to M; module by module	
• Group error		Yes	
• Overflow/Underflow		Yes; module-wise	
Diagnostics indication LED			
• Monitoring of the supply voltage (PWR-LED)		Yes; green LED	
• Channel status display		Yes; green LED	
• for channel diagnostics		No	
• for module diagnostics		Yes; green/red DIAG LED	
Potential separation			
Potential separation channels			
• between the channels		No	
• between the channels and backplane bus		Yes	
• between the channels and the power supply of the electronics		No	
Isolation			
Isolation tested with		707 V DC (type test)	
Standards, approvals, certificates			
Ecological footprint			
• environmental product declaration		Yes	
Global warming potential			
— global warming potential, (total) [CO2 eq]		9.32 kg	
— global warming potential, (during production) [CO2 eq]		4.97 kg	
— global warming potential, (during operation) [CO2 eq]		4.79 kg	
— global warming potential, (after end of life cycle) [CO2 eq]		-0.449 kg	
Security			
signed firmware update		Yes; firmware V2.0.0 or higher	
safely removing data		Yes; firmware V2.0.0 or higher	
data integrity		Yes; firmware V2.0.0 or higher	
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.		-30 °C; < 0 °C as of FS04	
• horizontal installation, max.		60 °C	
• vertical installation, min.		-30 °C; < 0 °C as of FS04	
• vertical installation, max.		50 °C	
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.		5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual	
Absolute humidity			
• dew point, min.		-60 °C; suitable for dry room applications	
Dimensions			
Width		15 mm	
Height		73 mm	
Depth		58 mm	
Weights			
Weight, approx.		31 g	
Classifications			
		Version	Classification
	eClass	16	27-24-26-01

eClass	14	27-24-26-01
eClass	12	27-24-26-01
eClass	9.1	27-24-26-01
eClass	9	27-24-26-01
eClass	8	27-24-26-01
eClass	7.1	27-24-26-01
eClass	6	27-24-26-01
ETIM	10	EC001596
ETIM	9	EC001596
ETIM	8	EC001596
ETIM	7	EC001596
IDEA	4	3562
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval



[Miscellaneous](#)

[Manufacturer Declaration](#)



[Metrological Approval](#)

General Product Approval



[China RoHS](#)



General Product Approval

EMV

For use in hazardous locations



[FM](#)

[CCC-Ex](#)



For use in hazardous locations

Maritime application

[Type Examination Certificate](#)



[Miscellaneous](#)

[CCC-Ex](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)

Maritime application

Environment

[KR \(Korean Register of Shipping\)](#)



Siemens EcoTech



last modified:

3/10/2026

