



Figure similar

SIMATIC ET 200SP, TM PTO 2x24 V, interface module for stepper drives, 2 channels pulse train output, PTO: 24 V, 2 DI, 1 DQ 24 V DC per channel, suitable for BU type A0

General information	
Product type designation	TM PTO 2x24V
usable BaseUnits	BU type A0
Color code for module-specific color-coded label	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	Yes
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	STEP 7 V17 with HSP or higher
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.35
Supply voltage	
Rated value (DC)	24 V
Load voltage L+	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	19.2 V
• permissible range, upper limit (DC)	28.8 V
• Reverse polarity protection	Yes
Input current	
Current consumption, max.	50 mA; without load
Power loss	
Power loss, typ.	1.5 W
Address area	
Address space per module	
• Inputs	32 byte
• Outputs	16 byte
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
Digital inputs	
Number of digital inputs	6; 3 per channel
Digital inputs, parameterizable	Yes
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Digital input functions, parameterizable	
• Synchronization	Yes
• Probe	Yes
• Drive ready	Yes
Input voltage	

- Rated value (DC) - for signal "0" - for signal "1" - permissible voltage at input, min. - permissible voltage at input, max.	24 V -5 ... +5 V +11 to +30V -30 V; -5 V continuous, -30 V brief reverse polarity protection 30 V
Input current	
for signal "1", typ.	2.5 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; none / 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms
Cable length	
- shielded, max. - unshielded, max.	1 000 m 600 m
Digital outputs	
Number of digital outputs	6; 3 per channel
Current-sinking	Yes; push-pull outputs for 24 V PTO outputs
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
Short-circuit protection	Yes; electronic/thermal
Response threshold, typ.	1 A
Controlling a digital input	Yes
Digital output functions, parameterizable	
- PTO (pulse train output) signal interface — 24 V asymmetrical - PTO (pulse train output) signal type — Pulse and direction — Count up, count down — Incremental encoder (A, B phase shift) — Incremental encoder (A, B phase shift, quadruple)	Yes Yes Yes Yes Yes Yes
Switching capacity of the outputs	
- with resistive load, max. - on lamp load, max.	0.1 A; 0.5 A for CHn.ED 1 W; 5 W for CHn.ED
Load resistance range	
- lower limit - upper limit	240 Ω; 48 ohms for CHn.ED 12 kΩ
Output voltage	
for signal "1", min.	23.2 V; L+ (-1.3 V), L+ (-0.8 V) for CHn.ED
Output current	
- for signal "1" rated value - for signal "1" permissible range, max. - for signal "1" minimum load current - for signal "0" residual current, max.	0.1 A; 0.5 A for CHn.ED 0.12 A; 0.6 A for CHn.ED 2 mA 0.5 mA
Switching frequency	
- with resistive load, max. - with inductive load, max. - on lamp load, max. - For signal interface 24 V asymmetrical	10 kHz 0.5 Hz; According to IEC 60947-5-1, DC-13 10 Hz 200 kHz; For 24 V PTO outputs
Total current of the outputs	
Current per module, max.	1.4 A
Cable length	
shielded, max.	600 m; Up to 10 kHz, 50 m at 200 kHz
Interfaces	
Number of RS 485 interfaces	0
Interrupts/diagnostics/status information	
Alarms	
Diagnostic alarm	Yes
Diagnoses	
- Monitoring the supply voltage - Short-circuit	Yes Yes

Diagnostics indication LED			
Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED		
Channel status display	Yes; green LED		
for module diagnostics	Yes; green/red DIAG LED		
Potential separation			
Potential separation channels			
between the channels and backplane bus	Yes		
Isolation			
Isolation tested with	707 V DC (type test)		
Standards, approvals, certificates			
Suitable for safety functions	No		
Ambient conditions			
Ambient temperature during operation			
horizontal installation, min.	-30 °C		
horizontal installation, max.	60 °C; Observe derating		
vertical installation, min.	-30 °C		
vertical installation, max.	50 °C; Observe derating		
Altitude during operation relating to sea level			
Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual		
Absolute humidity			
dew point, min.	-60 °C; suitable for dry room applications		
Decentralized operation			
to SIMATIC S7-300	Yes; Via control and feedback interface		
to SIMATIC S7-400	Yes; Via control and feedback interface		
to SIMATIC S7-1200	Yes		
to SIMATIC S7-1500	Yes		
to standard PROFIBUS master	Yes; Via control and feedback interface		
to standard PROFINET controller	Yes; Via control and feedback interface		
Dimensions			
Width	15 mm		
Height	73 mm		
Depth	58 mm		
Weights			
Weight, approx.	45 g		
Classifications			
		Version	Classification
	eClass	16	27-24-26-05
	eClass	14	27-24-26-05
	eClass	12	27-24-26-05
	eClass	9.1	27-24-26-05
	eClass	9	27-24-26-05
	eClass	8	27-24-26-05
	eClass	7.1	27-24-26-05
	eClass	6	27-24-26-05
	ETIM	10	EC001601
	ETIM	9	EC001601
	ETIM	8	EC001601
	ETIM	7	EC001601
	IDEA	4	3567
	UNSPSC	15	32-15-17-05
Approvals / Certificates			
General Product Approval			



[Miscellaneous](#)

[Manufacturer Declaration](#)



General Product Approval

EMV



[China RoHS](#)



For use in hazardous locations



[CCC-Ex](#)

[FM](#)



[Type Examination Certificate](#)

[Miscellaneous](#)

For use in hazardous locations



[CCC-Ex](#)

last modified:

1/22/2026