

Siemens
EcoTech



SIMATIC ET 200SP, BaseUnit BU20-P16+A0+2D, BU-TYPE U0, Packaging Unit:
1 Pieces, Push-in terminals, w/o AUX-terminals, new potential group, WxH: 20mm
x 117mm



General information	
Product type designation	BU type U0
HW functional status	FS10 and higher
Supply voltage	
Rated value (DC)	See manual
• For P1 and P2 bus	120 V
• For AUX bus	120 V; Equal potential group to P1/P2 bus or PE
• for process terminals	120 V
Rated value (AC)	See manual
• For P1 and P2 bus	277 V
• For AUX bus	277 V; Equal potential group to P1/P2 bus or PE
• for process terminals	277 V
external protection for power supply lines	Yes
Mains filter	
• integrated	No
Current carrying capacity	
up to 60 °C, max.	10 A
For P1 and P2 bus, max.	10 A
For AUX bus, max.	10 A
For process terminals, max.	10 A; Point of contact, derating depends on the module
Hardware configuration	
Automatic encoding	Yes
Formation of potential groups	
• New potential group	Yes
• Potential group continued from the left	No
Slots	
• Number of slots	1
Potential separation	
between backplane bus and supply voltage	Yes
between process terminals and supply voltage	Yes; Not applicable for process terminals 15 and 16
between power bus and supply voltage	No
Isolation	
Isolation tested with	3 100 V DC
Standards, approvals, certificates	
Ecological footprint	
• environmental product declaration	Yes

Global warming potential	
— global warming potential, (total) [CO2 eq]	0.873 kg
— global warming potential, (during production) [CO2 eq]	0.866 kg
— global warming potential, (during operation) [CO2 eq]	0 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.0011 kg

Ambient conditions

Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C

Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	3 000 m

Absolute humidity	
• dew point, min.	-60 °C; suitable for dry room applications

Connection method

Terminals	
• Terminal type	Push-in terminal
• system-integrated shield connection	Yes; Optional
• Conductor cross-section, min.	0.14 mm²; 0.2 mm² without wire end ferrule
• Conductor cross-section, max.	2.5 mm²; 1.5 mm² with wire end ferrule
• Number of process terminals to I/O module	16
• Number of terminals to AUX bus	0
• Number of add-on terminals	0
• Number of terminals with connection to P1 and P2 bus	2

Dimensions

Width	20 mm
Height	117 mm
Depth	35 mm

Weights

Weight, approx.	50 g
-----------------	------

Classifications

	Version	Classification
eClass	16	27-24-26-03
eClass	14	27-24-26-03
eClass	12	27-24-26-03
eClass	9.1	27-24-26-03
eClass	9	27-24-26-03
eClass	8	27-24-26-03
eClass	7.1	27-24-26-03
eClass	6	27-24-26-03
ETIM	10	EC001598
ETIM	9	EC001598
ETIM	8	EC001598
ETIM	7	EC001598
IDEA	4	3560
UNSPSC	15	32-15-17-04

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)



General Product Approval	For use in hazardous locations	Maritime application
--------------------------	--------------------------------	----------------------



[FM](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



Maritime application	Environment
----------------------	-------------

[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)



Siemens
EcoTech



last modified:

2/1/2026