



SIMATIC ET 200SP, spare part Server module for ET 200SP

General information			
Product type designation	Server module		
Installation type/mounting			
Mounting	Mounting rail 7.5 mm and 15 mm		
Input current			
Current consumption, max.	30 mA		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.	-30 °C		
• horizontal installation, max.	60 °C		
• vertical installation, min.	-30 °C		
• vertical installation, max.	50 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual		
Absolute humidity			
• dew point, min.	-60 °C; suitable for dry room applications		
Dimensions			
Width	7 mm		
Height	117 mm		
Depth	36 mm		
Weights			
Weight, approx.	19 g		
Classifications			
		Version	Classification
	eClass	16	27-24-26-92
	eClass	14	27-24-26-92
	eClass	12	27-24-26-92
	eClass	9.1	27-24-26-92
	eClass	9	27-24-26-92
	eClass	8	27-24-26-92
	eClass	7.1	27-24-26-92
	eClass	6	27-24-26-92
	ETIM	10	EC002584
	ETIM	9	EC002584
	ETIM	8	EC002584
	ETIM	7	EC002584

IDEA	4	3552
UNSPSC	15	32-15-17-03

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)



General Product Approval

For use in hazardous locations



[CCC-Ex](#)

[FM](#)

For use in hazardous locations

Maritime application



[Miscellaneous](#)

[Type Examination Certificate](#)

[CCC-Ex](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



Maritime application

[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)

last modified:

2/1/2026