



SIMATIC cable grip for SIMATIC BusAdapter, 5 units

General information			
Product type designation	Strain relief for PROFINET		
Ambient conditions			
Ambient temperature during operation			
• min.	0 °C		
• max.	60 °C		
Absolute humidity			
• dew point, min.	-60 °C; suitable for dry room applications		
Dimensions			
Width	15.5 mm		
Height	51.4 mm		
Depth	45 mm		
Width of cable tie, rec.	2.5 mm		
Width of cable tie, max.	7 mm		
Length of cable tie, min.	60 mm		
Classifications			
		Version	Classification
	eClass	16	27-24-26-92
	eClass	14	27-24-26-92
	eClass	12	27-24-26-92
	eClass	9.1	27-24-26-92
	eClass	9	27-24-26-92
	eClass	8	27-24-26-92
	eClass	7.1	27-24-26-92
	eClass	6	27-24-26-92
	ETIM	10	EC002584
	ETIM	9	EC002584
	ETIM	8	EC002584
	ETIM	7	EC002584
	IDEA	4	3552
	UNSPSC	15	32-15-17-03
Approvals / Certificates			
General Product Approval			

[Manufacturer Declaration](#)

last modified:

2/1/2026 