

product type designation

product description



IE FC TP Standard Cable GP 4x2 (AWG 24, Type C)

Shielded TP installation cable (8-core), sold by the meter, unassembled

Industrial Ethernet FastConnect TP standard cable GP 4x 2, TP installation CAT6A cable for connection to IE FC RJ45 plug 4x 2, AWG24, sold by the meter, delivery unit max. 2000 m minimum order quantity 20 m.

product brand name

SIMATIC NET

Technical Product Detail Page

<https://l.siemens.com/1P6XV1878-2A>

suitability for use

Standard cable with rigid cores for fast, permanent installation

cable designation

SF/UTP, 2YH (ST) CY 4x2x0,5/1,0 GN

wire length

sold by the meter

electrical data

attenuation factor per length

• at 10 MHz / maximum	0.058 dB/m
• at 100 MHz / maximum	0.191 dB/m
• at 250 MHz / maximum	0.311 dB/m
• at 300 MHz / maximum	0.343 dB/m
• at 500 MHz / maximum	0.453 dB/m

impedance

• at 1 MHz ... 100 MHz	100 Ω
------------------------	-------

near-end crosstalk per length

• at 1 MHz ... 100 MHz	0.453 dB/m
• at 1 MHz ... 250 MHz	0.393 dB/m
• at 1 MHz ... 300 MHz	0.381 dB/m
• at 1 MHz ... 500 MHz	0.348 dB/m

coupling loss / at 30 MHz ... 100 MHz / minimum

80 dB

transfer impedance per length / at 10 MHz

20 mΩ/m

loop resistance per length / maximum

190 mΩ/m

insulation resistance coefficient

5000 GΩ·m

operating voltage

• RMS value	80 V
• maximum	80 V

NVP value in percent

67 %

mechanical data

number of electrical cores

8

design of the shield

SF/UTP, overlapped aluminum-clad foil, sheathed in a protective braided shield of tinned copper wires

type of electrical connection / FastConnect

Yes

core diameter

• of AWG24 insulated conductor	0.51 mm
--------------------------------	---------

outer diameter

• of inner conductor	0.51 mm
• of the wire insulation	1 mm

• of the inner sheath of the cable	6.1 mm
• of cable sheath	8 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.2 mm
material	
• of the wire insulation	polyethylene (PE)
• of the inner sheath of the cable	FRNC
• of cable sheath	PVC
color	
• of the insulation of data wires	white-blue/blue, white-orange/orange, white-green/green, white-brown/brown
• of cable sheath	green
bending radius	
• with single bend / minimum permissible	24 mm
• with multiple bends / minimum permissible	40 mm
tensile load / maximum	100 N
weight per length	74.5 kg/km
ambient conditions	
ambient temperature	
• during operation	-40 ... +85 °C
• during storage	-40 ... +80 °C
• during transport	-40 ... +80 °C
• during installation	-40 ... +80 °C
ambient condition / for operation	Temperature range for permanent installation -40 °C to +85 °C
fire behavior	flame resistant according to IEC 60332-3-24 (Category C)
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil	oil resistant according to IEC 60811-2-1 (4 h / 70°C)
• to grease	Conditional resistance
• to water	conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
• halogen-free	No
• PoE capability	Yes
• PoE+ capability	Yes
• PoE++ capability	Yes
• silicon-free	Yes
wire length / for Industrial Ethernet	
• with 100BaseTX	100 m
• with 1000BaseT	100 m
• for 10GBase T	90 m
test voltage	
• at AC / core-to-core	2000 V
• at AC / core shield	2000 V
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(UL)us, CMG, AWM-Style 21500, cRU AWM I A/B 60°C 300V FT2
UL/ETL style / 600 V Rating	No
certificate of suitability	
• EAC approval	Yes
• CE marking	Yes
• RoHS conformity	Yes
product conformity	
• ANSI/TIA-EIA 568-B.2 Cat.5e	Yes
• IEC 61784-5-2-CP 2/2 (Ethernet/IP)	Yes
standard for structured cabling	Cat6A
• resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No

- French marine classification society (BV)
- Det Norske Veritas (DNV)
- Germanische Lloyd (GL)
- Lloyds Register of Shipping (LRS)
- Nippon Kaiji Kyokai (NK)
- Polski Rejestr Statkow (PRS)

No
No
No
No
No
No

further information / internet links

internet link

- to website: Selection guide for cables and connectors
- to web page: selection aid TIA Selection Tool
- to web page: SiePortal
- to website: Image database
- to website: CAX-Download-Manager
- to website: Industry Online Support

<https://support.industry.siemens.com/cs/ww/en/view/109766358>
<https://www.siemens.com/tstcloud>
<https://sieportal.siemens.com/>
<https://www.automation.siemens.com/bilddb>
<https://www.siemens.com/cax>
<https://support.industry.siemens.com>

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)



[Declaration of Conformity](#)



[Fire safety / Physical security](#)

General Product Approval

Test Certificates

other

Environment

[China RoHS](#)



[Declaration of Conformity](#)

[Special Test Certificate](#)

[Miscellaneous](#)

[Environmental Confirmations](#)

Environment

Industrial Communication

[Environmental Confirmations](#)

[PROFINET](#)

last modified:

3/10/2026