

Class49 Pilot Light Kit-24V-240



product brand name	Enclosed Control Product Accessories
design of the product	22 mm Green Fwd/Rev or High/Low Pilot Light, 24 to 240 V AC/DC
product type designation	Pilot light
special product feature	Full voltage type
General technical data	
Height x Width x Depth [in]	4 × 2.2 × 1.6 in
touch protection against electrical shock	finger-safe
ambient temperature [°F]	
• during storage	-13 ... +176 °F
• during operation	-4 ... +140 °F
ambient temperature	
• during storage	-25 ... +80 °C
• during operation	-20 ... +60 °C
country of origin	Mexico
accessories / included	Wires
control voltage / at AC / rated value	19.2 ... 288 V
Lamp	
number of lampholders	2
number of indicator lights	2
type of light source	LED
Lens	
color / of the cover cap	Red
model of the lens	rectangular
material / of the lens	Plastic
Legend	
material	Synthetic paper label with adhesive back
marking / of inscription plate	FOR, REV, LOW, HIGH
color / of inscription plate	White foreground / Black background
Mounting/wiring	
fastening method	Bracket for use with enclosures with lift-off covers
type of electrical connection	screw terminal
tightening torque [lbf·in] / with screw-type terminals	7 ... 8 lbf·in
type of connectable conductor cross-sections / for AWG cables / for control connection / with screw-type terminals / single or multi-stranded	2x (18 ... 16 AWG)
temperature / of the conductor / for control connection / with screw-type terminals / maximum permissible	75 °C
material / of the conductor	CU
Certificates/ approvals	
certificate of suitability	cULus

Further information

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:49SDLB7GU>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/US2:49SDLB7GU>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_us.aspx?mlfb=US2:49SDLB7GU&lang=en

last modified:

10/23/2025 