



30mm BlackMax, Epoxy Coated Corrosion Resistant Metal Operator, Round Push-Pull Operator Non-Illuminated Mushroom Head Cap Large 2 1/2" (63.5 mm) Plastic, Red 2 Position Maintained, Pull-to-Release UL Listed, CSA Certified NEMA 1,3,3R,4,4X,12,13 & Automotive Standards

|                                           |                           |
|-------------------------------------------|---------------------------|
| design of the product                     | Actuator round            |
| <b>Enclosure</b>                          |                           |
| number of command points                  | 1                         |
| delivery state as a kit                   | No                        |
| <b>Actuator</b>                           |                           |
| material of the actuating element         | plastic                   |
| type of unlocking device                  | pull-to-unlatch mechanism |
| number of switching positions             | 2                         |
| <b>Front ring</b>                         |                           |
| product component front ring              | Yes                       |
| design of the front ring                  | standard                  |
| material of the front ring                | metal                     |
| color of the front ring                   | black                     |
| <b>Holder</b>                             |                           |
| material of the holder                    | Metal                     |
| <b>General technical data</b>             |                           |
| product component                         |                           |
| • light source                            | No                        |
| degree of pollution                       | 1                         |
| protection class IP                       | IP66                      |
| Net Weight                                | 0.03 kg                   |
| <b>Ambient conditions</b>                 |                           |
| ambient temperature                       |                           |
| • during operation                        | -35 ... +70 °C            |
| • during storage                          | -40 ... +85 °C            |
| <b>Installation/ mounting/ dimensions</b> |                           |
| shape of the installation opening         | round                     |
| <b>Further information</b>                |                           |

### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

### Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52BP2V2>

### Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52BP2V2>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/US2:52BP2V2>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=US2:52BP2V2&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:52BP2V2&lang=en)

---

last modified:

10/23/2025 