



30mm BlackMax, Epoxy Coated Corrosion Resistant Complete Metal Unit  
Illuminated Push-Pull Operator Full Voltage, 24V AC/DC Incandescent Lamp  
Mushroom Head Cap Small 1 3/4" (44.5 mm) Plastic, Amber 3 Position Pull-  
Momentary/Push-Maintained 1 N.C.+1 N.C. Extra Late Break Heavy Duty  
Contacts, A600/P600 UL Listed, CSA Certified NEMA 1,3,3R,4,4X,12,13 &  
Automotive Standards

General technical data

|            |         |
|------------|---------|
| Net Weight | 0.23 kg |
|------------|---------|

Further information

- Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
- Information for data generation and storage  
<https://support.industry.siemens.com/cs/ww/en/view/109995012>
- Information- and Downloadcenter (Catalogs, Brochures,...)  
<https://www.siemens.com/ic10>
- Industry Mall (Online ordering system)  
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52BP7DTU>
- Cax online generator  
<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52BP7DTU>
- Service&Support (Manuals, Certificates, Characteristics, FAQs,...)  
<https://support.industry.siemens.com/cs/ww/en/ps/US2:52BP7DTU>
- Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)  
[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=US2:52BP7DTU&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:52BP7DTU&lang=en)

last modified: 10/23/2025 