



Siemens Low Voltage Circuit Protection General Duty Safety Switches. Type: ENCLOSED, SAFETY SWITCH Std: UL V. Rating: 240VAC A. Rating: 30 A No. Of Poles: 3P F. Rating: 60Hz Action: SINGLE THROW Material: STEEL Enclosure: TYPE 1. 2-3 point mounting holes. O. Cycles: 10000 O. Temperature: (-20F-120F) AMBIENT TEMPERATURE Environmental Conditions: INDOOR

General technical data	
principle of operation of the actuating element	SINGLE THROW
mechanical service life (operating cycles) typical	10000
product function note	
number of poles	3
Electricity	
ampacity	30 A
Environmental conditions	
ambient temperature during operation maximum	49 °C
ambient temperature during operation minimum	-29 °C
Model	
product brand name	Siemens
product type designation	ENCLOSED/SAFETY SWITCH
Mechanical Design	
design of the housing	TYPE 1
material	STEEL
General product approval	
certificate of suitability	UL

last modified:

9/15/2021 

