

wire connector TC1.0 14 AWG...8 AWG Cu with control wire voltage tap 4 units
accessory for: 3VA51



Model	
product brand name	SETRON
product designation	circular conductor terminal
accessories	Wire connector
General technical data	
designation / of the terminal	TC1.0
type of electrical connection / with control wire tap	Yes
Connections according IEC	
stripped length	12,2 mm
Connections according UL	
permissible temperature / of connectable conductor / according to UL 486A-486B	90 °C
stripped length	0.48 in
connectable conductor cross-section	
• for copper cable / solid / minimum	14 AWG
• for copper cable / solid / maximum	10 AWG
• for copper cable / stranded / minimum	14 AWG
• for copper cable / stranded / maximum	8 AWG
tightening torque / when using copper cables	
• solid	14 AWG: 20 lb-in, 12-10 AWG: 35 lb-in
• stranded	14 AWG: 20 lb-in, 12-10 AWG: 35 lb-in, 8 AWG: 55 lb-in
Certificates	
General Product Approval	EMV



[Miscellaneous](#)



Maritime application	other	Environment			
	Confirmation	Miscellaneous	Environmental Con- firmations	Environmental Con- firmations	

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875 Information for data generation and storage https://support.industry.siemens.com/cs/ww/en/view/109995012

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9134-0JK10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9134-0JK10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9134-0JK10

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

8/8/2025 

