



Figure similar

Indicator light, 16 mm, round, plastic, yellow, smooth, for inscription with insert caps

|                                                                |                      |
|----------------------------------------------------------------|----------------------|
| product brand name                                             | SIRIUS               |
| product designation                                            | Indicator lights     |
| design of the product                                          | Single device round  |
| product type designation                                       | 3SB2                 |
| Enclosure                                                      |                      |
| number of command points                                       | 0                    |
| Actuator                                                       |                      |
| design of the actuating element                                | indicator light      |
| product extension optional light source                        | No                   |
| color of the actuating element                                 | yellow               |
| material of the actuating element                              | plastic              |
| shape of the actuating element                                 | Smooth lens          |
| outer diameter of the actuating element                        | 19 mm                |
| type of unlocking device                                       | without              |
| number of switching positions                                  | 0                    |
| Front ring                                                     |                      |
| product component front ring                                   | No                   |
| Holder                                                         |                      |
| material of the holder                                         | Plastic              |
| General technical data                                         |                      |
| product function                                               |                      |
| • EMERGENCY OFF function                                       | No                   |
| • EMERGENCY STOP function                                      | No                   |
| protection class IP                                            | IP65                 |
| vibration resistance according to IEC 60068-2-6                | 20 ... 200 Hz: 5g    |
| reference code according to IEC 81346-2                        | P                    |
| Substance Prohibitance (Date)                                  | 07/01/2006           |
| Net Weight                                                     | 0.004 kg             |
| Connections/ Terminals                                         |                      |
| tightening torque of the screws in the bracket maximum         | 0.4 N·m              |
| Ambient conditions                                             |                      |
| ambient temperature                                            |                      |
| • during operation                                             | -25 ... +70 °C       |
| • during storage                                               | -40 ... +80 °C       |
| environmental category during operation according to IEC 60721 | 3K6                  |
| Installation/ mounting/ dimensions                             |                      |
| fastening method                                               | front plate mounting |

|                                   |       |
|-----------------------------------|-------|
| shape of the installation opening | round |
| mounting diameter                 | 16 mm |
| mounting height                   | 9 mm  |
| installation width                | 19 mm |
| installation depth                | 50 mm |

Approvals Certificates

|                          |                   |
|--------------------------|-------------------|
| General Product Approval | Test Certificates |
|--------------------------|-------------------|



[Special Test Certificate](#)

[Miscellaneous](#)

|                   |       |             |
|-------------------|-------|-------------|
| Test Certificates | other | Environment |
|-------------------|-------|-------------|

[Type Test Certificates/Test Report](#)



[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage  
<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)  
<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)  
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB2001-6CD06>

Cax online generator  
<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB2001-6CD06>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)  
<https://support.industry.siemens.com/cs/ww/en/ps/3SB2001-6CD06>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)  
[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SB2001-6CD06&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB2001-6CD06&lang=en)

last modified: 4/2/2025