



Figure similar

OUTPUT CHOKE; PHASES:3; UN1(V):800; ITHMAX 1(A) / F1(HZ):60F(HZ):600; F TAKT(KHZ):4; I LN (A):54; LN(MH):0,35; UK(%):17,1; TA/ISOKL:40 /H; IP00; TYPE OF TERMINALS:SCREW CONNECTION; EN 61558-2-20 >CHOKE<

General technical data		
product designation		output reactor
product brand name		SIDAC
phase number		3
type of voltage		AC
operating voltage rated value		
• maximum	V	800
operating frequency rated value		
• minimum	Hz	600
• maximum	Hz	600
•		
— operational current at AC rated value	A	54
— current at AC maximum	A	60
inductivity rated value	H	0.00035
power loss [W] of the coil	W	120
power loss [W] of the iron core	W	105
clock frequency		
• rated value	Hz	4 000
Mechanical data		
type of electrical connection for main current circuit		screw-type terminals
width	m	0.3
height	m	0.26
depth	m	0.21
Ambient conditions		
thermal class according to IEC 60085		H
ambient temperature rated value	°C	40
protection class IP		IP00
Certificates/ approvals		
General Product Approval	other	Environment



[Confirmation](#)[Environmental Confirmations](#)

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4EU3052-0ED00-4CA0>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EU3052-0ED00-4CA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4EU3052-0ED00-4CA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EU3052-0ED00-4CA0&lang=en

last modified:

4/1/2025 