



SIMATIC ET 200SP, 5 BU covers, 20mm for protection of empty slots

Figure similar

General information			
Product type designation		BU cover	
Ambient conditions			
Ambient temperature during operation			
• min.		-40 °C	
• max.		70 °C	
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.		5 000 m; Restrictions for installation altitudes > 2 000 m, see manual	
Dimensions			
Width		20 mm	
Height		73 mm	
Depth		35.3 mm	
Classifications			
		Version	Classification
	eClass	14	27-24-26-92
	eClass	12	27-24-26-92
	eClass	9.1	27-24-26-92
	eClass	9	27-24-26-92
	eClass	8	27-24-26-92
	eClass	7.1	27-24-26-92
	eClass	6	27-24-26-92
	ETIM	10	EC002584
	ETIM	9	EC002584
	ETIM	8	EC002584
	ETIM	7	EC002584
	IDEA	4	3552
	UNSPSC	15	32-15-17-03
	Approvals / Certificates		
General Product Approval		Railway	

[Manufacturer Declaration](#)

[Miscellaneous](#)

[KC](#)

[Confirmation](#)

