



SIMATIC ET 200SP, 500 labeling strips, yellow, roll with 500 strips

| General information                        |                                 |         |                |
|--------------------------------------------|---------------------------------|---------|----------------|
| Product type designation                   | Labeling strips, foil           |         |                |
| Ambient conditions                         |                                 |         |                |
| Ambient temperature during operation       |                                 |         |                |
| • min.                                     | 0 °C                            |         |                |
| • max.                                     | 60 °C                           |         |                |
| Mechanics/material                         |                                 |         |                |
| Color                                      | Yellow                          |         |                |
| Dimensions                                 |                                 |         |                |
| Width                                      | 13 mm                           |         |                |
| Height                                     | 31 mm                           |         |                |
| Outer diameter of the thermal printer roll | 70 mm                           |         |                |
| Inner diameter of roll                     | 40 mm                           |         |                |
| Width of the thermal printer roll          | 62 mm                           |         |                |
| Scope of supply                            |                                 |         |                |
| Delivery quantity in pieces                | 1                               |         |                |
| Components included                        | 500; Individual labels per role |         |                |
| • Number of individual strips              |                                 |         |                |
| Classifications                            |                                 |         |                |
|                                            |                                 | Version | Classification |
|                                            | eClass                          | 14      | 27-24-26-92    |
|                                            | eClass                          | 12      | 27-24-26-92    |
|                                            | eClass                          | 9.1     | 27-24-26-92    |
|                                            | eClass                          | 9       | 27-24-26-92    |
|                                            | eClass                          | 8       | 27-24-26-92    |
|                                            | eClass                          | 7.1     | 27-24-26-92    |
|                                            | eClass                          | 6       | 27-24-26-92    |
|                                            | ETIM                            | 10      | EC002584       |
|                                            | ETIM                            | 9       | EC002584       |
|                                            | ETIM                            | 8       | EC002584       |
|                                            | ETIM                            | 7       | EC002584       |
|                                            | IDEA                            | 4       | 3552           |
|                                            | UNSPSC                          | 15      | 32-15-17-03    |
| Approvals / Certificates                   |                                 |         |                |
| General Product Approval                   |                                 |         |                |

---

last modified:

5/22/2024 